


## Electrothermal Electromantle Extraction Heaters



The Electrothermal Electromantle Extraction Heater with three and six recesses has a built-in electronic controller and offers a choice of heater only or heater/stirrer combination.

Vented case's unique air flow ensures the case remains "cool-to-the-touch."

### Heater and Heater/Stirrer Models (As Shown in Images Above)

- Individual built-in solid state electronic controls enable easy regulation of heater, while removing sparking associated with mechanical switching
- Three 12.7mm(0.5in) diameter support rods are included
- Top cover is polypropylene and external surfaces are powder coated and resistant to most chemical solutions
- Coiled heating element is suspended within a thermal insulating cartridge to provide maximum heat transfer and support, while removing sparking associated with mechanical switching
- Heater cartridge is easy to replace
- Earth (ground) screen encloses the heater for added safety
- Pilot lights indicate when power is on and supplied to heaters and supplied to stirrers

### Heater/Stirrer Models (As Shown in Images Above)

- Stirrer models include a stirring speed of 50 to 1000rpm
- One stirring control operates each set of three recesses
- Stirring Module allows the solution to be stirred and heated simultaneously

**Warranty:** One year parts and labour

**Certification:** CE

### Thermo Scientific Electromantle Extraction Heaters 3 Recess Model

Cat. No.	Specifications	Flask Capacity	Interior DxWxH	No. of Circuits	Electrical Requirements	Watts	Shipping Weight
Max. Element Temperature					450°C		
Heating Model Only	Material		Polypropylene Top on Stove		Painted aluminium		
EME3 0100/CEB		3x100ml	26x63x9cm (10.23x24.80x3.54in)	3	230v 50/60Hz	180w	6kg (13 lbs)
EME3 0100/CEBX1		3x100ml	26x63x9cm (10.23x24.80x3.54in)	3	115v 50/60Hz	180w	6kg (13 lbs)

EME3 0100/CEBX6	3x100ml	26x63x9cm (10.23x24.80x3.54in)	3	230v 50/60Hz, EU Plug	180w	6kg (13 lbs)
EME3 0250/CEB	3X250ml	26x63x9cm (10.23x24.80x3.54in)	3	230v 50/60Hz	450w	7kg (15.4lbs)
EME3 0250/CEBX1	3x250ml	26x63x9cm (10.23x24.80x3.54in)	3	115v 50/60Hz	450w	7kg (15.4lbs)
EME3 0250/CEBX6	3x250ml	26x63x9cm (10.23x24.80x3.54in)	3	230v 50/60Hz, EU Plug	450w	7kg (15.4lbs)
EME3 0500/CEB	3x500ml	26x63x9cm (10.23x24.80x3.54in)	3	230v 50/60Hz	600w	7.4kg(16 lbs)
EME3 0500/CEBX1	3x500ml	26x63x9cm (10.23x24.80x3.54in)	3	115v 50/60Hz	600w	7.4kg(16 lbs)
EME3 0500/CEBX6	3x500ml	26x63x9cm (10.23x24.80x3.54in)	3	230v 50/60HZ, EU Plug	600w	7.4kg(16 lbs)
EME3 1000/CEB	3x1000ml	26x63x9cm (10.23x24.80x3.54in)	3	230v 50/60Hz	900w	7.4kg(16 lbs)
EME3 1000/CEBX1	3x1000ml	26x63x9cm (10.23x24.80x3.54in)	3	115v 50/60Hz	900w	7.4kg(16 lbs)
EME3 1000/CEBX6	3x1000ml	26x63x9cm (10.23x24.80x3.54in)	3	230v 50/60HZ, EU Plug	900w	7.4kg(16 lbs)

## Thermo Scientific Electromantle Extraction Heaters 6 Recess Model

Cat. No.	Flask	Interior DxWxH	No. of	Electrical	Watts	Shipping
Specifications	Capacity		Circuits	Requirements		Weight
Heat. Mag. Model Only	Temperature			450°C		
Material						
EME6 0100/CEB	6x100ml	26x120x9cm (10.23x47.24x3.54in)	6	230v 50/60Hz, EU Plug	420w	11.1kg (24.7lbs)
EME6 0100/CEBX1	6x100ml	26x120x9cm (10.23x47.24x3.54in)	6	115v 50/60Hz	420w	11.1kg (24.7lbs)
EME6 0100/CEBX6	6x100ml	26x120x9cm (10.23x47.24x3.54in)	6	230v 50/60Hz, EU Plug	420w	11.1kg (24.7lbs)
EME6 0250/CEB	6X250ml	26x120x9cm (10.23x47.24x3.54in)	6	230v 50/60Hz	900w	10kg (22lbs)
EME6 0250/CEBX1	6x250ml	26x120x9cm (10.23x47.24x3.54in)	6	115v 50/60Hz	900w	10kg (22lbs)
EME6 0250/CEBX6	6x250ml	26x120x9cm (10.23x47.24x3.54in)	6	230v 50/60Hz, EU Plug	900w	10kg (22lbs)
EME6 0500/CEB	6x500ml	26x120x9cm (10.23x47.24x3.54in)	6	230v 50/60Hz	1200w	12.5kg (28lbs)
EME6 0500/CEBX1	6x500ml	26x120x9cm (10.23x47.24x3.54in)	6	115v 50/60Hz	1200w	12.5kg (28lbs)
EME6 0500/CEBX6	6x500ml	26x120x9cm (10.23x47.24x3.54in)	6	230v 50/60HZ, EU Plug	1200w	12.5kg (28lbs)
EME6 1000/CEB	6x1000ml	26x120x9cm (10.23x47.24x3.54in)	6	230v 50/60Hz	1800w	12.5kg (28lbs)
EME6 1000/CEBX1	6x1000ml	26x120x9cm (10.23x47.24x3.54in)	6	115v 50/60Hz	1800w	12.5kg (28lbs)
EME6 1000/CEBX6	6x1000ml	26x120x9cm (10.23x47.24x3.54in)	6	230v 50/60HZ, EU Plug	1800w	12.5kg (28lbs)



Thank you for reading this data sheet.

For pricing or for further information, please contact us at our UK Office, using the details below.



**UK Office**

**Keison Products,**

**P.O. Box 2124, Chelmsford, Essex, CM1 3UP, England.**

**Tel: +44 (0)330 088 0560**

**Fax: +44 (0)1245 808399**

**Email: [sales@keison.co.uk](mailto:sales@keison.co.uk)**

Please note - Product designs and specifications are subject to change without notice. The user is responsible for determining the suitability of this product.