

Data Sheet

Mixing / Magnetic Stirrers



big squid IKAMAG® white

The improved magnetic stirrer now in new design.

new: Digital speed display (LED)

new: Electronically controlled motor for more capacity

new: Higher speed range from 0 - 2.500 rpm

- Outstanding chemical resistance due to glass top and synthetic bottom made of TPC-ET

- Recyclable materials

Accessories: IKAFLON® 15 Magnetic stirring bar, IKAFLON® 30 Magnetic stirring bar, IKAFLON® 10 Magnetic stirring bar, IKAFLON® 25 Magnetic stirring bar, TRIKA® 25 Magnetic stirring bar, RSE Stirring bar remover, IKAFLON® 20 Magnetic stirring bar

Technical Data	
Number of stirring positions	1
Stirring quantity max. per stirring position (H ₂ O) [l]	1.5
Stirring quantity max. (H ₂ O) [l]	1
Motor rating input [W]	3
Motor rating output [W]	2
Speed display	LED
Speed range [rpm]	0 - 2500
Stirring bar length max. [mm]	30
Speed control	50 RPM Steps
Set-up plate material	glass
Set-up plate dimensions [mm]	Ø 160
Dimensions (W x H x D) [mm]	180 x 40 x 195
Weight [kg]	0.7
Permissible ambient temperature [°C]	5 - 40
Permissible relative moisture [%]	80
Protection class according to DIN EN 60529	IP 54
RS 232 interface	no
Analog output	no
Frequency [Hz]	50/60
Power input [W]	4
DC Voltage [V=]	12
Current consumption [mA]	300
Ident. No.	3672000



Thank you for reading this data sheet.

For pricing or for further information, please contact us at our UK Office, using the details below.



UK Office

Keison Products,

P.O. Box 2124, Chelmsford, Essex, CM1 3UP, England.

Tel: +44 (0)330 088 0560

Fax: +44 (0)1245 808399

Email: sales@keison.co.uk

Please note - Product designs and specifications are subject to change without notice. The user is responsible for determining the suitability of this product.