

Data Sheet



C-MAG MS 10 IKAMAG®

New magnetic stirrer without heating. With ceramic set-up plate which offers excellent chemical resistance.

- Powerful motor for stirring quantities of up to 15 I (H2O)
- Elevated control panel for protection against leaking liquids

Accessories: IKAFLON® 10 Magnetic stirring bar, IKAFLON® 15 Magnetic stirring bar, IKAFLON® 20 Magnetic stirring bar, IKAFLON® 25 Magnetic stirring bar, IKAFLON® 30 Magnetic stirring bar, IKAFLON® 40 Magnetic stirring bar, IKAFLON® 50 Magnetic stirring bar, IKAFLON® 80 Magnetic stirring bar, TRIKA® 25 Magnetic stirring bar, TRIKA® 40 Magnetic stirring bar, RS 1 Set of magnetic stirring bars, RSE Stirring bar remover, H 16 V Support rod

Technical Data	
Number of stirring positions	1
Stirring quantity max. per stirring position (H2	2O) [l] 15
Stirring quantity max. (H2O) [I]	15
Motor rating input [W]	15
Motor rating output [W]	1.5
Speed display	scale
Speed range [rpm]	100 - 1500
Stirring bar length max. [mm]	80
Speed control	scale 0 - 6
Set-up plate material	ceramic
Set-up plate dimensions [mm]	260 x 260
Dimensions (W x H x D) [mm]	300 x 105 x 415
Weight [kg]	6
Permissible ambient temperature [°C]	5 - 40
Permissible relative moisture [%]	80
Protection class according to DIN EN 60529	IP 21
Voltage [V]	230
Frequency [Hz]	50/60
Power input [W]	30
Ident. No.	3582600



Thank you for reading this data sheet.

For pricing or for further information, please contact us at our UK Office, using the details below.

UK Office Keison Products,

P.O. Box 2124, Chelmsford, Essex, CM1 3UP, England.

Tel: +44 (0)330 088 0560 Fax: +44 (0)1245 808399

Email: sales@keison.co.uk

Please note - Product designs and specifications are subject to change without notice. The user is responsible for determining the suitability of this product.