

Overhead Stirrers

Overhead stirrers are useful where mixing of a higher viscosity material is required, the three models available from Stuart® increase in torque to suit even the most demanding laboratory application.

Page 70 - General purpose overhead stirrer

- High performance overhead stirrer

Page 71 - Dual torque overhead stirrer

Page 72 - Stands

- Stirrer Paddles



Overhead Stirrers

Overhead stirrer, general purpose, SS10

high-torque-low

- Used with volumes up to 15 litres
- Aqueous to low viscosity liquids
- Keyless chuck
- Quiet running
- Budget price

Easy to use general purpose overhead stirrer suitable for day to day laboratory use with aqueous and low viscosity liquids such as light oils, up to 15 litres. With good speed control and overload protection usually found in more advanced models, the SS10 represents excellent value for money.

Overhead stirrer, high performance, SS20

- Used with volumes up to 25 litres
- Low to medium viscosity liquids
- Hollow shaft
- Keyless chuck

A powerful stirrer designed for demanding laboratory applications. Suitable for stirring liquids up to medium viscosity, including oils and microbiological media, up to 25 litre capacity. Features a hollow shaft arrangement to facilitate easy adjustment of paddle height. Advanced overload protection and sophisticated, responsive speed control.

Technical Specification

| | SS10 | SS20 |
|----------------------------|----------------------|----------------------|
| Speed range | 100 - 2000rpm | 100 - 2000rpm |
| Max. viscosity | 10,000mPas | 20,000mPas |
| Torque at chuck | 15Ncm | 27Ncm |
| Chuck range | 1.5 - 13mm dia | 1.5 - 13mm dia. |
| Hollow shaft | No | 3 - 8mm dia. |
| Dimensions, mm (w x d x h) | 85 x 175 x 230 | 85 x 195 x 230 |
| Net weight, kg | 2.7 | 3.2 |
| Electrical supply | 230V, 50 / 60Hz, 50W | 230V, 50 / 60Hz, 80W |
| IP Rating | 42 | 42 |

Ordering Information

| Model | Description |
|-------|------------------------------------|
| SS10 | Overhead stirrer, general purpose |
| SS20 | Overhead stirrer, high performance |







Overhead stirrer, dual torque, SS30

- Used with volumes up to 40 litres
- Medium to high viscosity liquids
- Two modes of torque for extra power
- Keyless chuck

A versatile heavy duty stirrer with the ability to mix high viscosity liquids, including heavy oils, up to 40 litres. This stirrer has two modes of operation, which can be easily alternated, offering maximum versatility.

Overhead Stirrers

Mode 1 has high torque at lower speed for stirring very viscous liquids.

Mode 2 has lower torque at higher speed and provides brisk mixing of medium viscosity liquids.

Advanced overload protection and sophisticated, responsive speed control. The stirrer also features a hollow shaft for use with long paddles.

Technical Specification

| | SS30 |
|----------------------------|--------------------------|
| Speed range | 50 - 500 / 100 - 2000rpm |
| Max. viscosity | 40,000mPas |
| Torque at chuck | 90 / 27Ncm |
| Chuck range | 1.5 - 13mm dia. |
| Hollow shaft | 3 - 8mm dia. |
| Dimensions, mm (w x d x h) | 85 x 195 x 230 |
| Net weight, kg | 3.8 |
| Electrical supply | 230V, 50 / 60Hz, 80W |
| IP Rating | 42 |


Ordering Information

| Model | Description | |
|-------|-------------------------------|--|
| SS30 | Overhead stirrer, dual torque | |

A range of stands and stirrer paddles are also available. See page 72.

See page 116 for S.I. Base and S.I. Derived Units.

Viscosity mPas Torque Ncm



Torque profile of Stuart overhead stirrers

Overhead Stirrers

Stands

Extra strong retort stands with H-pattern base for stability and robust support rod. Both versions include bosshead. Heavy duty stand recommended for use with SS30 overhead stirrer.

high-torque-low

Technical Specification

| | SS10/1 | SS10/2 |
|----------------------|----------------|----------------|
| Base, mm (w x d x h) | 400 x 350 x 25 | 550 x 480 x 25 |
| Rod, mm (dia. x l) | 16 x 700 | 25 x 850 |
| Net weight, kg | 7.6 | 20.2 |

Ordering Information

| Model Description | |
|-------------------|------------------------|
| SS10/1 | Stand, general purpose |
| SS10/2 | Stand, heavy duty |

Stirrer paddles

Made from high grade stainless steel, there is a choice of five paddle heads and two lengths of 8mm diameter paddle rod.

The heads screw on and off the rods, so they can be mixed and matched depending upon stirring requirements.

This gives maximum versatility and value for money.

For complete paddle, order rod plus head(s).

Technical Specification

Paddle rods

| | SS10/5 | SS10/6 |
|----------|--------|--------|
| Diameter | 8mm | 8mm |
| Length | 350mm | 550mm |

Paddle heads

| | SS10/10 | SS10/11 | SS10/12 | SS10/13 | SS10/14 |
|-------------|---------|---------|---------|---------|---------|
| Total width | 60mm | 94mm | 80mm | 50mm | 60mm |

Ordering Information

| Model | Description |
|--------------------|----------------------------------|
| SS10/5 | Paddle rod, 350mm |
| SS10/6 | Paddle rod, 550mm |
| SS10/10 | Small paddle head |
| SS10/11 | Large paddle head |
| SS10/12 | Large propeller head (2 blade) |
| SS10/13 SS10/14 | Small propeller head (4 blade) |
| 5510/14 | Anchor paddle head |







Thank you for reading this data sheet.

For pricing or for further information, please contact us at our UK Office, using the details below.

UK Office Keison Products,

P.O. Box 2124, Chelmsford, Essex, CM1 3UP, England.

Tel: +44 (0)330 088 0560

Fax: +44 (0)1245 808399

Email: sales@keison.co.uk

Please note - Product designs and specifications are subject to change without notice. The user is responsible for determining the suitability of this product.