



C-MAG HS 4 IKAMAG®

New magnetic stirrer with heating and ceramic heating plate which offers excellent chemical resistance.

- Powerful motor for stirring quantities of up to 5 l (H₂O)
- Fixed safety circuit of 550 °C
- Hot Top indicator >> hot surface warning to prevent burns!
- Exact temperature setting via digital display (LED)
- Digital error code display
- Elevated control panel for protection against leaking liquids

Accessories: H 38 Holding rod, H 44 Boss head clamp, IKAFLON® 10 Magnetic stirring bar, IKAFLON® 15 Magnetic stirring bar, IKAFLON® 20 Magnetic stirring bar, IKAFLON® 25 Magnetic stirring bar, IKAFLON® 30 Magnetic stirring bar, TRIKA® 25 Magnetic stirring bar, RS 1 Set of magnetic stirring bars, RSE Stirring bar remover, H 16 V Support rod

Technical Data

Number of stirring positions	1
Stirring quantity max. per stirring position (H ₂ O) [l]	5
Stirring quantity max. (H ₂ O) [l]	5
Motor rating input [W]	15
Motor rating output [W]	1.5
Speed display	scale
Speed range [rpm]	100 - 1500
Heat output [W]	250
Heating rate (1 l H ₂ O in H15) [K/min]	2.5
Heating temperature range [°C]	50 - 500
Heat control	LED
Heat control accuracy [±K]	10
Speed control	scale 0 - 6
Fixed safety circuit [°C]	550
Set-up plate material	ceramic
Set-up plate dimensions [mm]	100 x 100
Dimensions (W x H x D) [mm]	150 x 105 x 260
Weight [kg]	3
Permissible ambient temperature [°C]	5 - 40
Permissible relative moisture [%]	80
Protection class according to DIN EN 60529	IP 21
Voltage [V]	230
Frequency [Hz]	50/60
Power input [W]	270
Ident. No.	3581000



Thank you for reading this data sheet.

For pricing or for further information, please contact us at our UK Office, using the details below.



UK Office

Keison Products,

P.O. Box 2124, Chelmsford, Essex, CM1 3UP, England.

Tel: +44 (0)330 088 0560

Fax: +44 (0)1245 808399

Email: sales@keison.co.uk

Please note - Product designs and specifications are subject to change without notice. The user is responsible for determining the suitability of this product.